

Electronic dial gauge

MarCator 1086 R



Application:

For static measurements of lengths and length differences

Version:

- Factor adjustable
- Large LCD display (11 mm)
- mm/inch switch-over
- LOCK function (key lock)
- Permissible deviation MPEp for increment 0.0005=2 µm, for increment 0.01=20 µm

Delivery:

In case with CR 2450 battery



Art. no.	33166 120
Length measuring range	25 mm
Digit increment	0.01 mm
Min./max. measurement force	0.65-1.15 N
Error limit	20 µm
Repeat accuracy	10 µm
Data transmission type	multiCOM
IP protection class	IP 42
Absolute function	Yes
Automatic switch-off	Yes
Preset function	Yes
Tolerance value entry	Yes
Calibration Group	CE
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2450N lithium
Rotating housing	Yes
Reversible counting direction	Yes
Calibration Group Description	Dial gauge
WEEE (taking back waste electrical and electronic equipment)	5

EAN-Code

4059192014407