

## META CLIP boltless rack with shelves

Load capacity per bay 100/230 kg, plastic coated



### Application:

Universal rack system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools.

### Execution:

- Double-row boltless rack with pre-assembled frame = clinched frame
- Both rows securely connected on the back
- Shelves height-adjustable, spacing 25 mm
- Shelves with a 50 mm hole grid to accommodate accessories
- Basic rack planning dimensions: Nominal length + 56 mm, 2 x nominal depth + 75 mm

### Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



|   |                  |
|---|------------------|
| <b>Art. no.</b>                         | <b>50167 730</b> |
| <b>Brand</b>                            | META             |
| <b>Manufacturer Part Number</b>         | 20070780         |
| <b>Height</b>                           | 3000 mm          |
| <b>Length</b>                           | 1356 mm          |
| <b>Depth</b>                            | 836 mm           |
| <b>Nominal length</b>                   | 1300 mm          |
| <b>Nominal depth</b>                    | 800 mm           |
| <b>Design</b>                           | Shelving unit    |
| <b>Type of assembly</b>                 | To insert        |
| <b>Surface</b>                          | Plastic-coated   |
| <b>Design of the frame</b>              | Pre-assembled    |
| <b>Grid dimension</b>                   | 25 mm            |
| <b>Number of shelves</b>                | 6 PCS            |
| <b>Load-carrying capacity per shelf</b> | 230 kg           |
| <b>Load-carrying capacity per field</b> | 1900 kg          |
| <b>Number of frame</b>                  | 2 PCS            |
| <b>Quality label</b>                    | RAL-RG 6 14/ 1   |
| <b>Made in</b>                          | Germany          |
| <b>Gross Weight</b>                     | 158.522 kg       |
| <b>Product Group</b>                    | 508              |

### EAN

40262 12 102642