

Platform trolley series 600, 2 longitudinal walls, zinc plated

The surface of the loading area is covered with sheet steel, load capacity 500 kg



Execution:

- The surface of the loading area is covered with 2 mm electrolytically zinc-plated sheet steel
- Loading area height 260 mm
- Longitudinal walls made of melamine-coated MDF board, height 400 mm
- Push handle made of 25 mm steel tubing
- 2 fixed castors and 2 castors made of solid rubber 200 x 50 mm
- The 600 series includes platform trolleys, table trolleys, platform trolleys with front wall, box trolleys and bar-type trolleys.



Art. no.	50260 028
Brand	KONGAMEK
Manufacturer Part Number	KM635-2HB
Material of loading surface	Steel plate
Type	With 400 mm box body
Load-carrying capacity	500 kg
Length	1000 mm
Width	700 mm
Height	900 mm
Loading surface length	1000 mm
Loading surface size	1000 x 700 mm
Loading-surface height	260 mm
Loading-surface width	700 mm
Length x width x height	1000 x 700 x 900 mm
Number of fixed rollers	2
Number of steering rollers	2
With wheel lock	Yes
Wheel width	50 mm
Wheel diameter	200 mm
Material of wheel	Solid rubber
Colour	Silver coloured
Surface	Zinc plated
Gross Weight	47.000 kg
Product Group	5AT

EAN

7350050357887