

Wooden step ladder, two-sided access

Execution:

- Solid coniferous sawn timber side-rails, beech wood steps
- 80 mm deep, grooved steps
- Top two rungs made of beech, 22 x 44 mm
- Mortised step/side-rail connection, resulting in a smooth side-rail surface
- Stable steel horseshoe hinges
-
-
- Firmly screwed-in textile straps to prevent spreading
- Plastic transport lock on ladder feet
- Step spacing: 250 mm
- Ladder inclination: 70°
- With practical bucket hook as standard



Art. no.	59002 471
Brand	MUNK GÜENZBURGER STEIGTECHNIK
Manufacturer Part Number	33810
Number of steps	2 x 5
Length as standard ladder	1.39 m
Working height	2.71 m
Step distance	250 mm
Length (folded together)	1.39 m
Pedestal width	0.53 m
Weight	9.2 kg
Accessibility	Both sides
Max. load capacity	150 kg
Step depth	80 mm
Rail height	65 mm
Length	1.39 m
Material	Wood
Width (top)	0.43 m
Width (bottom)	0.53 m
Transport width	0.515 m
Transport length	1.23 m
Transport depth	0.17 m
Rail width	22 mm
Stride length	1.09 m
Gross Weight	7.000 kg
Product Group	5AP

EAN

4031405338104