

Lift lever chain hoist UNOplus

Compact, robust design

Yale

Application:

For tensioning, hoisting, pulling and tying down.

Execution:

- Compact and robust sheet steel housing
- Zinc-plated load chain in line with DIN EN 818-7 (quality class T)
- Smooth-running free-chaining feature for rapid load attachment
- 360° rotating carrying hook
- Chain end made of shatter-proof plastic
- Automatic threaded mechanical brake

Advantage:

- low tare weight
- Requires low lifting power



Art. no.	77157 050
Brand	YALE
Manufacturer Part Number	2300161
Model	UNOplus 750
Load-carrying capacity	750 kg
Nominal chain thickness	18 mm
Chain diameter	6 mm
Stroke force at nominal load	20 daN
Length of lever	250 mm
Stroke height per lever revolution	20 mm
Lift height	1500 mm
Min. hook spacing	340 mm
Number of load chains	1 PCS
EN standard	818-7
Gross Weight	7.643 kg
Product Group	7EE

EAN

4053981988719