

## Data sheet

### Article Description

#### NRGkick Fix Select, for fixed connection with lockable wall socket 230 V/16 A, Type 9332

- Socket overheating protection
- Plug protection with arc protection
- Protective conductor test by means of loop impedance
- Thermo-Protect temperature management
- False installation test
- Temperature monitoring at each plug attachment and phase pin
- Domestic plug overheating protection on both pins
- Phase shift detection
- Blackout protection (Protection from power cuts)
- Energy meter
- Theft-proof
- Over- and undervoltage protection
- Drive-over proof
- Access to all information with NRGkick App

### Article Picture



### Technical Data:

**Nominal voltage:** 230 V/400 V/50 Hz

**Nominal current:** 32 A

**Max. charging power:** 22 kW

**RCD (AC):** 30 mA

**RCD (DC):** 6 mA

**IP protection class:** IP67

**Shock+impact resistant:** IK10

**Operating conditions:** - 40 ° C - + 70 ° C,  
(Norm: + 45 ° C)


**Humidity:** 5 %- 95 %

**Sea level:** max. 4.000 m

**Weight(5 m cable):** approx. 3.9 kg

**Dimensions (Unit):** LWH 216 x 90 x 64 mm

**Connection technologies:** WLAN 2,4 Ghz,  
Bluetooth Low Energy (BLE)



Wall socket  
230 V/16 A

### In a practical set consisting of:

NRGkick without plug attachment, wall socket 16 A, interlocked protective cover

inter BÄR-No.	Cable length
9332-001.01	with 5 m cable
9332-002.01	with 7.5 m cable

Technical modifications reserved!

Works at 230 V-mains must only be carried out by a specialist!