


## Synergy 21 LED LoRa (433MHZ) PAR56 Pool Light 27W RGB+CCT \*Milight/Miboxer\*



kwh/1000h:	29,70
Lumen:	2000
Watt:	27,0
Nennlebensdauer:	35000 Std.
Schaltzyklen:	50000
Opt. Umgebungstemp.:	25 °C



Product Name: 27W RGB+CCT PAR56 LED Pool Light  
 Model No.: PW01  
 Input Voltage: AC12V / DC12~24V  
 Power: 27W  
 Working Temperature: -20~45?  
 Color temperature: 2700~6500K  
 Luminous Flux: 2000LM  
 Light Efficiency: 75LM/W  
 CRI: >80  
 Control distance: 50m (Lamps into 0.5m underwater)  
 Lifespan: 50000h  
 Beam Angle: 160°  
 IP Rate: IP68  
 Housing Material: 316 Stainless Steel+PC


Energieeffizienzklasse: A  
 kWh/1000h: 29,7

### Merkmale

Merkmal	Wert
Abstrahlwinkel:	160

Merkmal	Wert
CC oder CV:	CV
Dimmbar:	Ja
Grösse:	177*102
LED - Gehäusematerial:	Stahl
Lichtfarbe:	RGB-WW
Lichtfarbe in Kelvin:	2700~6500
Lumen:	2000
Schutzklasse:	IP68
Volt:	12/24
Gewicht:	0.7 Kg

## Weitere Bilder



## 433MHz Remote control Smart phone APP control

433MHz remote or smart phone APP control to fulfill more function settings.  
\*Smart phone APP controlling need 433MHz gateway



## Many colors change randomly

16 million colors, color temperature, brightness and saturation adjust randomly

16 million  
colors change

CCT  
Adjustable

Dimmable  
Saturation control

## Switch-OFF to change colors function

Switch OFF and ON to change the colors and dynamic modes in turn




## High lumen LED Chips

High lumen LED chips; low power consumption  
and low light failure



## High quality PC cover

Strong hardness, high lighting transmitting rate; Wide illumination distance



## 316 stainless steel lamp housing

316 stainless steel materials, not easy to fade; Long lifespan



## Zubehör

Art.-Nr.

Name

178058

Synergy 21 LED LoRa (433MHZ) Controller DMX über LoRa \*Milight/Miboxer\*