

Crimp Fittings

Press-armaturen


Emboutsertis

Raccordi a graffare

Racores para presión

BP

BSP Male Parallel
 Außengewindeanschluss/BSP
 Mâle BSP cylindrique, cone 60°
 Maschio gas
 Macho fijo/BSP



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting			mm			mm	mm	mm	mm			mm
1G4BP4	1S4BP4	1A4BP4	G 1/4				-4	44,3	20,9		4,2	19		
1G4BP5	1S4BP5	1A4BP5	G 1/4				-5	45,1	21,2		5,3	19		
1G6BP6	1S6BP6	1A6BP6	G 3/8				-6	48,4	23,1		6,7	22		
1G8BP6	1S8BP6	1A8BP6	G 1/2				-6	52,4	27,1		6,7	27		
1G8BP8	1S8BP8	1A8BP8	G 1/2				-8	58,0	28,3		9,6	27		
1G10BP10	1S10BP10	1A10BP10	G 5/8				-10	61,9	32,5		12,8	30		
1G12BP12	1S12BP12	1A12BP12	G 3/4				-12	63,1	32,9		15,5	32		
1G16BP16	1S16BP16	1A16BP16	G 1				-16	70,9	36,5		20,7	41		
1G20BP20	1S20BP20	1AP20BP20*	G 1 1/4				-20	86,2	42,2		26,6	50		
		1AT20BP20**	G 1 1/4				-20	86,2	42,2		26,6	50		
1G24BP24	1S24BP24	1A24BP24	G 1 1/2				-24	92,6	46,3		32,0	55		
1G32BP32	1S32BP32	1A32BP32	G 2				-32	103,6	53,4		44,4	70		

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire