

## Product information


# 97 52 20

## Crimping Pliers

Short design

- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force due to lever action for fatigue-reduced operation
- Good handling due to 20° angled head, low weight and short design
- Special quality chrome vanadium electric steel, oil-hardened



General	
Article No.	97 52 20
EAN	4003773026853
Pliers	burnished
Head	burnished
Handles	with multi-component grips
Weight	380 g
Dimensions	195 x 77 x 20 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable
Technical details	
	
Application	Coax-, BNC- and TNC-connectors RG 58/59/62/71/223
Number of crimping positions	3
Capacity SW mm	5.4 mm / 6.48 mm / 1.72 mm
Sleeves (diameter)	Ø 6.4 / 7.6 / 2.1 mm

*technical change and errors excepted*

