





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/16/02	MCCORMICK
B	ECN# 1605 ADDED COMPONENT SPECIFICATIONS	12/09/03	MCCORMICK
C	ECN# 2082 CORRECTING DIM LENGTH	05/24/05	M.LAHEY




2X TYPE 1 JACK

TABLE	
J1	J2
PIN 1	PIN 1
PIN 2	PIN 2
PIN 3	PIN 5
PIN 4	PIN 6
PIN 5	PIN 3
PIN 6	PIN 4
SHELL	SHELL



RECOMMENDED PANEL CUT OUT



Component Specifications	
<b>Material</b>	
Housing	ABS 94V-0 Rating
Connector	Plastic; PBT with Glass Fiber
Contact	Brass
Shell	Brass
PCB	Epoxy Glass FP-4 94V-0 Rating
<b>Finish</b>	
Housing	Chrome
Contact	Gold 30 Micro Inch
Shell	Nickel
<b>Electrical</b>	
Current Rating	2 AMP Max
Voltage Rating	140 VDC
<b>Environmental</b>	
Operating Temperature	-20°C to +80°C

CS-132

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES  
TOLERANCES ARE:  
X ±.1  
XX ±.05  
XXX ±.005  
CABLE LENGTH TOLERANCE  
≤300' ±5% >300' ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	01/13/2002
CHECKED BY D.PARHAM	01/13/2002
APPROVED BY R.CARRICK	01/13/2002

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

<b>L-com</b> CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION COUPLER PANEL MOUNTED FIREWIRE1/1 SHIELDED			
DRAWING TITLE <b>OUTLINE DRAWING</b>			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>ECF504-94MS-OD1</b>	REV. <b>C</b>
SCALE: NONE		CAD FILE: ECF504-94MS-OD1.SLDDRW	SHEET 1 OF 1