

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 850
Brand	AMF
Manufacturer Part Number	8 1075
DIN	787
Thread dimension	M20
Groove width	22 mm
Length excluding head	200 mm
Outer diameter	21.7 mm
Thread length	125 mm
Length of head	35 mm
Head height	14 mm
Gross Weight	0.747 kg
Product Group	260

EAN

4020772081072