

Balancer with extending pneumatic hose, load capacity 0.4-3.0 kg

Type 7223, cable extraction 800 mm

AUTOSTAT

Execution:

- Air supply via the AIR spring balance by installed compressed air hose directly to the compressed air machine
- Rate of air flow is identical in inserted and extracted hose
- Rotating joint for air connection is integrated in the device
- hose reel is particularly soft and free-moving
- Housing and hose drum made of extremely shock-resistant and abrasion-proof special plastic
- Safety device: freely rotating and swivelling suspension with a screw snap hook, fall protection in line with DIN 15112 included in scope of delivery, carrying capacity adjusted via notches, tools attached using quick-action coupling provided, adjustable elastic cable retraction limiter, riveted special motive spring
- Working area: Hose extension: 800 mm

Delivery:

Available upon request: Hose extensions



Art. no.	77000 652
Brand	AUTOSTAT
Manufacturer Part Number	77000652
Min./max. load-carrying capacity	1.2-2.2 kg
Model	7223/2
Spring design	Special mainspring
Cord in-feed restriction	Absorbs impacts, adjustable
Material of cable drum	Plastic
With automatic locking	No
Max. hose extension length	800 mm
Inner hose diameter	6 mm
Outer diameter of hose	8 mm
Max. operating pressure	10 bar
Suspension type	Freely rotating and pivot screw karabiner hook
Load attachment	Screw Karabiner hook
Material of housing	Plastic
Housing width	141 mm
Housing thickness	71 mm
Height	385 mm
DIN	15112
Gross Weight	1.451 kg
Product Group	772

EAN

4039247421787