

Product type designation

Product description

Distance piece MDS D124/D324/D424/RF320T

Support for mounting transponders with 27 mm diameter and 15 mm distance to metal

MOBY D/RF300 ISO/RF200 Spacer for MDS D124/D324/D424/D524 and RF320T Diameter 35 mm; Height 15 mm; Temperature range up to +180 °C Packing unit = Minimum order quantity: 20 units



Suitability for use

Complete configuration of an OCR application

Mechanical data

Material

PPS

Color

black

Permitted ambient conditions

Ambient temperature

- during operation -25 ... +180 °C
- during storage -40 ... +180 °C
- during transport -40 ... +180 °C

Design, dimensions and weight

Height

22 mm

Diameter

36 mm

Further Information / Internet Links

Internet-Link

- to website: TIA Selection Tool

<http://www.siemens.com/tia-selection-tool>

- to website: Selector SIMATIC NET SELECTION TOOL
- to the website: IWLAN
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

last modified:

<https://support.industry.siemens.com/WW/view/en/67384964>

<http://www.siemens.com/iwlan>

<http://www.siemens.com/ident/rfid>

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

11/15/2018