

## Product MD 577 Y3

5 mm LED indicator  
color yellow

product-catalog	5 mm LED indicator
color	yellow
part no	MD 577 Y3
forward current [mA]	12-16
forward voltage typ. [V]	24-28
wavelength [nm]	585
rec. mounting hole Ø [mm]	6.35
panel thickness [mm]	1 .. 3
operating temperature [°C]	-25 .. +80
storage temperature [°C]	-30 .. +85

chip construction	GaAsP
forward current max. [mA]	25
reverse voltage max. [V]	4
luminous intensity typ. [mcd]	30

Low cost LED indicator with ribbed nylon body for easy front panel mounting

150 mm PVC leads \*, AWG 26, black lead, cathode lead = blue  
\* for special lead length add appendix -Lxxx (xxx length in mm) to standard P/N

### note

- all dimension are in millimeter
- tolerance is  $\pm 0.25$  mm unless otherwise noted
- specifications are subject to change without notice
- version 1.0

