



REVISED	DR	APP



Length
0.3m+/-10mm
0.5m+/-10mm
1m+/-15mm
1.5m+/-20mm
2m+/-30mm
3m+/-50mm
5m+/-80mm
7m+/-100mm
10m+/-150mm



Electrical character:
 1. 100% Open/short/Intermittent testing
 2. TEST FLUKE CHANNEL PASS

Note: (Colour Codes)

- White RAL 9003
- Black RAL 9005
- Grey RAL 7044 (standard)

Connection: RJ45 PLUG - RJ 45 PLUG

Cable diameter: 3,5mm

Unshielded

Gold Plated contacts

Data transfer rate: up to 1 Gbps

Cable must pass Fluke test



1	CABLE	PATCHCABLE SLIMLINE CAT 6 250 MHz. U/UTP AWG 30/7 (7/0.10BC) x 4P; PVC OD:3.5 +/- 0.15mm
2	CONNECTORS	SHORT RJ45 8P8C FU* (COLOR: BLUE)
3	MOLDING	PVC 75A
NO	PART NAME	

DESCRIPTION		PATCHCABLE SLIMLINE CAT 6			
SIZE	A4	DATE	13.01.2016	CHECKED	TOL
UNIT	MM	DRAWN	R.Hueller	APPROVED	08-22300
CUSTOM TARIF NO.: 85444290900					