

**Outdoor Recessed Brick Light 3.8W 3000K 180lm IP65***Partcode: ILBLA015 / Page: 1*

Discover Integral's new outdoor range. Light up the exterior of your home with these compact, stylish and contemporary LED luminaires. Weatherproof and hard-wearing, this range is designed to last against the elements while bringing a designer look to your surroundings.

Build your outdoor lighting into your wall for a clean, designer look. This low-energy, pre-wired brick light comes with the choice of two interchangeable bezels so you can personalise the look and effect of your wall lighting.

[Watch Video](#)

**Product Details**

Partcode: ILBLA015

Check Code: 274711

Range Name: Outdoor

Product Type: Outdoor

Warranty: 3 Years

CE / RoHS: Yes

**Physical Data**

Optic: Opal Polycarbonate diffuser

Material: Die cast aluminium body with powder coated finish

**Physical Data**

Length: 205mm  
Width: 95mm  
Depth: 65mm  
Weight (Unpackaged Single Unit): 340g  
Luminaire Fixing: Recessed


**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 3.8 Watts  
Driver included: Yes  
Electric Current: AC  
Frequency Range: 50/60 Hz  
Power Factor:  $\geq 0.80$   
Dimming: Non-dimmable  
LVD Certified: Yes  
EN: EN-60598

**Light Data**

Lumens: 180lm  
Lumens per Watt: 47.0lm/W  
Correlated Colour Temperature (CCT): 3,000k  
Colour Temperature: Warm White  
Colour Rendering Index (CRI):  $\geq 80$   
LED Type: Surface mounted device (SMD)  
Instant on - Less than 1 second: Yes  
Lifetime: 25,000 hrs  
Switching Cycles:  $>12,500$  X

## Environmental



Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 50 degrees

IP (Ingress Protection) Rating: IP65

Hg 0% (Mercury Free): Yes

## Packaging



EAN Barcode (unit of 1): 5055788232544

Packaged Weight (Unit of 1): 350g

Length (unit of 1): 210mm

Width (unit of 1): 100mm

Depth (unit of 1): 75mm

**Outer packaging info available on website**

*Product data last updated on: Thursday, October 25, 2018 - 16:13*