

Product information

95 16 165

Cable Shears

IEC 60900 DIN EN 60900

- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Clean and smooth cut without crushing and deformation
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- Easy cutting with one-hand operation
- With guard
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened



⚡ 1000 V

General	
Article No.	95 16 165
EAN	4003773039648
Shears	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	262 g
Dimensions	165 x 47 x 21 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple-stranded	50 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
AWG	1 / 0
VDE tested	yes

technical change and errors excepted



Cut performed with a Cable Shear: easy, clean cut without any deformation of the cable

