



12W

VT-822 12W LED WALL LIGHT COLORCODE:4000K WHITE BODY

Lumens 750	Beam Angle 140	Dimensions 130x160mm
----------------------	--------------------------	--------------------------------

Day White
SKU:8335

2 YEARS
WARRANTY



Technical Information

Watts:	12	IP Rating:	IP54
Lumens:	750	Dimmable:	No
On/Off Cycles:	>15000	Warranty (Years):	2
Beam Angle:	140	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	PC	Operation Temperature:	-20 to +45°c
Long life:	20,000 Hours	Input Power:	AC:100-240V,50/60Hz

Features

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- ✓ Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- ✓ Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

Packaging

Unit Details

Gross Weight(GW) Kgs 0.487

Unit CBM 0.002618

Listing Details

EAN Code 3800157632461

Commodity Code 9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton) 20

Qty Per Pallet 400

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES