

HSS metal circular saw blade

for universal use up to 1000 N/mm² on Eisele and Trennjäger machines

ORION[®]

Application:


for creating saw cuts on low-speed machines such as Eisele, Trennjäger and other brands.

Execution:

- precision-ground metal circular saw blade with Bw tooth type (curved tooth = alternate bevel) and C tooth type (with taper tap and third tap)

Advantage:

- innovative cutting geometry for cutting solid material with high cutting depths
- cut distribution enables high cutting performance
- steam-treated protects against metal welding



Art. no.	14015 326
Brand	ORION
Manufacturer Part Number	14015326
Tooth shape	C
Cutting material	HSS
Cutting edge diameter	370 mm
Bore diameter	50 mm
Thickness of cutting edge	3 mm
Teeth spacing	10 mm
Side holes	4/15/80, 4/14/85
Number of teeth	120
Gross Weight	2.264 kg
Product Group	1QK

EAN

4053625363728