

Micrometer

With cylindrical and spherical measuring faces

Mitutoyo

Application:

For measuring e.g. curved surfaces and wall thicknesses of pipes, bearings, rings, etc.

Version:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench



Art. no.	32016 635
Min./max. length measuring range	75-100 mm
Vernier scale	0.01 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Error limit	4 μ m
Display	Nonius
Calibration Group	D
Type	E – with spherical anvil
Min./max. measurement force	5-10 N

EAN-Code

4946368010441