

LED professional workshop lamp

cordless

ATORN®

Version

- robust, splash-proof housing with rubberised gripping surface
- 2 folding hooks that can be rotated by 360°
- 2 holding magnets on the back, 1 magnet on the bottom
- switch functions: 1. front auxiliary light, 2. 100% main light, 3. 50% main light, 4. off
- lamp base can be rotated by 180° and locked in eight positions
- with battery status and remaining charge indicator
- 3.7-V/2600-mAh Li-ion battery, charged via a 5-V Micro USB socket
- effective lighting duration of 6 hours, charging time of 4 hours



Art. No.	56829 025
Length	266 mm
Luminous flux	440 lm
Length x width x height	266 x 48 x 32 mm
IP protection class	IP 54

EAN-Code

4050293532333