

## Drill BEV 1300-2

1300 watts, 2-speed, in box

**metabo**<sup>®</sup>

### Delivery

in cardboard box



<b>Art. no.</b>	<b>70005 056</b>
<b>Brand</b>	METABO
<b>Manufacturer Part Number</b>	600574000
<b>Model</b>	BEV 1300-2
<b>Manufacturer Article Number</b>	600574000
<b>Nominal voltage</b>	230 V
<b>Max. drilling diameter in steel</b>	16 mm
<b>Max. drilling diameter in wood</b>	40 mm
<b>Power input</b>	1300 W
<b>Power output</b>	730 W
<b>Idle speed 1st gear min./max.</b>	0-1100 rpm
<b>Idle speed 2nd gear min./max.</b>	0-3100 rpm
<b>Cable length</b>	4 m
<b>Max. torque</b>	44 Nm
<b>Min./max. drill chuck span width</b>	1.5-13 mm
<b>Material of gear housing</b>	Aluminium die casting
<b>Drill chuck type</b>	Gear ring drill chuck
<b>Weight</b>	2.7 kg
<b>With rubber-coated handle</b>	Yes
<b>With overload protection</b>	Yes
<b>With restart protection</b>	Yes
<b>With right/left-hand rotation</b>	Yes
<b>With electronic feedback</b>	Yes
<b>With impulse function</b>	Yes
<b>Gross Weight</b>	3.670 kg
<b>Product Group</b>	745

### EAN

4007430314352