



Powerswitch for EM systems for SON

HID Power Switch PS 400 T05 220-230V 50/60Hz

Power-switches with internal timer for HID PS 400 T5 / HID PS R 400 T5

Product data

• General Characteristics

Rated Number of Lamps	1 piece
Rated Ballast-Lamp Power	70-400
Rated Lamptype	SON
Application code	400 T05
Line Voltage	220-230 V
Line Frequency	50/60 Hz

• Operating Characteristics

Mains voltage performance (AC)	-8%/+6%
--------------------------------	---------

• Wiring Characteristics

Connector type	Screw
Striplength	6.5 mm
Wcs Ballast contacts	0.75-2.50 mm ²

• Temperature Characteristics

T-case maximum	80 (max) °C
T-ambient	-30 (min), 70 (max) °C


• Product Dimensions

Length A1	74 mm
Length A3	62 mm
Width B1	36 mm
Height C1	32 mm


• Product Data

Order code	913700623491
Full product code	913700623491
Full product name	HID PS 400 T05 220-230V 50/60Hz
Order product name	HID PS 400 T05 220-230V 50/60Hz
Pieces per pack	1
Packing configuration	30
Packs per outerbox	30
Bar code on pack - EAN1	8711500911544
Bar code on outerbox - EAN3	8711500911551
Logistic code(s) - 12NC	913700623491
Net weight per piece	0.118 kg

Dimensional drawing



Product	A1 (Norm)	A3 (Norm)	B1 (Norm)	C1 (Norm)
HID PS 400 T05	74	62	36	32



Schematic of switch in combination with multiwattage ballast



© 2011 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2011, June 7
data subject to change