

5

4

3


2

1

SPECIFICATION

Performance level	PL2
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION dB
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB



Solder buckets for AWG 20 Max

ø3,1 ±0,1

8 ±0,2

33,3 ±0,15

24,7 ±0,2

12,5 ±0,4

4,9


8,2

39,1 ±0,4

27,5 ±0,3

10,8 ±0,3

2,84

			Dat.	Name	
			Detail.	8-JUL-02	
			Insp.	12/01/12	JB
			Stand.		
36283	12/01/12	SD	HARTING EURL F-95972 Paris		
33250	03/11/05	JMDR			
31058	8-JUL-02	CV			
Mod.	Dat.	Name			

All Dim. in mm
Orig. Size DIN A 4D-Sub, female, straight
15 Poles, turned solder
buckets, with holesMa?Mstab/
Scale

1.5:1

TB 09642117240

Blatt/ Page

1 / 1

Sub.

