


## MASI67 INSTALLATION TECHNOLOGY

Connection 2x profile- to 2x profile cable

MASI67 connection  
2 × on 2 × profile cable

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### Technical Data

Operating voltage	max. 36 V DC
Total current	max. 8 A
Isolation voltage	AS-Interface/Power: 200 V

#### General data

Protection	IP67
Mounting method	DIN-rail mountable (EN 60715) or screw fixing
Temperature range	-20...+60 °C (storage temperature -40...+80 °C)
Dimensions H × W × D	90×74×26 mm

**Commercial data**

country of origin	DE
customs tariff number	85369010
minimum order quantity	1