

## M8 MALE 0° FIELD-WIREABLE SCREW TERM.

3-pol. 0,14...0.5mm<sup>2</sup>

Male straight


3-pole


Screw terminals

Connection cross section: 0.14...0.5 mm<sup>2</sup>

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Form

08601

### Technical Data

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.14...0.5 mm <sup>2</sup>
Sealing range (cable diameter)	2.5...5.0 mm
Protection	IP67 inserted and tightened (EN 60529)

### General data

Temperature range	-25...+85 °C
Dimensions H × W × D	50×12×12 mm

### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1