



SAVI 7400 OFFICE SERIES

BENEFITS

- Keep your conversations private and clear with DECT™ Security and a noise-canceling microphone with acoustic fence technology.
- With 2x better density than other DECT™ headsets, more people in shared spaces benefit from wireless headsets with clear, interference-free audio.
- With 3-way connectivity, a universal base, and easy set-up and pairing, the Savi 7400 office series is the perfect solution for the modern office.

BUILT FOR THE MODERN OFFICE

Designed for the modern office with enhanced density performance, multi-device connectivity and advanced security features. You can deploy this headset across the company so everyone will benefit from increased productivity and wireless freedom.

- Connects to computer, desk phone and mobile
- Noise-canceling mic enhanced with Poly Acoustic Fence technology
- Conference up to 4 headsets onto a single base
- Designed to meet the DECT™ Security Step C – the highest security level from DECT™ Forum¹.

SAVI 7400 OFFICE SERIES



SAVI 7420 OFFICE



SAVI 7410 OFFICE

SPECIFICATIONS

CONNECTS TO

- Desk phone, PC, and mobile. For PC only, see the Savi 7300 UC Series

OFFICE BASE COMPATIBILITY

- Works with Savi 8400, Savi 8200, Savi 7400, and Savi 7300 Series headset tops

WIRELESS

- Technology: DECT™ 6.0 – North America only
- Technology: DECT™ – Outside North America
- Range: Line of sight up to 590 ft/180 m; Typical office environment up to 180 ft/55 m
- Security: Designed to meet Security Step C - the highest level from the DECT™ Forum
- Encryption: Military level FIPS 140-2 listed 256-AES encryption
- Authentication: 128-bit AES
- Density: Up to 2x more density than other DECT™ headsets
- Power: Adaptive power control to maximize user density

BATTERY

- Battery Capacity: 500mAh (Savi 7410 and Savi 7420)
- Battery Type: Technician replaceable lithium ion polymer
- Talk time: up to 13 hours
- Charge time: two hours full charge
- Standby time: up to 52 hours

RECEIVE FREQUENCY RESPONSE

- Wideband 100 - 6800Hz
- Multimedia 20Hz - 20kHz

HEARING PROTECTION

- SoundGuard DIGITAL: protects against sound levels above 118dBA; G616 antistartle (during calls) detects and eliminates any large sudden increase in signal level; Time-weighted average prevents average daily noise exposure from exceeding 85dBA²

MICROPHONE AND TECHNOLOGY

- Noise canceling with Acoustic Fence Technology
- Meets Microsoft Teams Open Office requirements

HEADSET CONTROLS AND LIGHTS

- Call answer/end, mute volume +/-, power on/off
- Combined call answer/end and Microsoft Teams button, mute volume +/-, power on/off (Microsoft Teams version only)
- In call indicator
- Multiple voice prompts — chosen language configurable via software

HEADSET BASE

- Works with Savi 8400, Savi 8200, Savi 7400, and Savi 7300 Series headset tops
- PC/Desk phone/Bluetooth® selector buttons
- Conference up to 4 headsets
- Color display for audio control settings
- Scroll Wheel
- Back Button
- Microsoft Teams Button (Microsoft Teams version only)

HEADSET WEIGHT

- Savi 7420 Over-the-head (binaural): 160 g /5.64 oz
- Savi 7410 Office Over-the-head (monaural): 120 g /4.23 oz

APPLICATIONS SUPPORTED

- Poly Lens
- Microsoft Teams Certified³

¹ DECT security standards can be found on <https://etsi.org>

² Requires Poly Lens software to enable SoundGuard DIGITAL features

³ Microsoft Teams versions only

LEARN MORE

To learn more information about Savi 7400 Office Series, visit poly.com