

Type ER precision collet chuck

GERC HP, DIN 6499/ISO 15488-B, concentricity of 2 µm

FAHRION®
FAR BEYOND PRECISION

Application:

For HSC machining with high-precision machining results.

Execution:


- HP collets with small concentricity and repeat tolerance of 2 µm (for system tolerance of 3 µm and with 3 x dia. maximum = 50 mm), clamp bridge h 10.
- For ATORN precision collet chucks and Fahrion CentroP precision spring collet chucks.
- With FAHRION | Protect corrosion protection for longer service life.
- Surface super-finished for enhanced retention force.

Advantage:

- Greater concentricity extends tool service life.
- Collets do not need to be replaced as often or can be used longer for specific applications.

Delivery:

1x type ER precision collet chuck.



Art. no.	23323 536
Brand	FAHRION
Manufacturer Part Number	13613010630
Collet type	426E GERC16-HP
Clamping diameter	6.3 mm
Min./max. clamping range	1-10 mm
Outer diameter	17 mm
Length	27.5 mm
Coolant supply	External
Clamping bypass	-1 mm
Gross Weight	0.025 kg
Product Group	235

EAN

4054631173677