

## Tool cabinet with shelves

Doors optionally with perforated panel, slotted panel or viewing window

<sup>®</sup>RasterPlan

### Application:

For secure and clearly-arranged storage of high-quality tools.

### Version:

- Welded sheet steel frame with perforated rear wall throughout with 10 x 10 mm perforation grid, for attaching support elements
- Overlay double-walled, twist-resistant hinged doors, opening angle over 200°
- Doors lockable with bascule lock engaging on 3 sides

|   |  |
|---|--|
| <b>Art. no.</b>                         | <b>50639 227</b>                           |
| <b>Door design</b>                      | Slotted plates                             |
| <b>Width</b>                            | 1000 mm                                    |
| <b>Depth</b>                            | 500 mm                                     |
| <b>Height</b>                           | 1950 mm                                    |
| <b>Number of shelves</b>                | 2 PCS                                      |
| <b>Shelf width</b>                      | 1000 mm                                    |
| <b>Shelf depth</b>                      | 500 mm                                     |
| <b>Load-carrying capacity per shelf</b> | 80 kg                                      |
| <b>With partition wall</b>              | No   |
| <b>Central locking</b>                  | Yes  |
| <b>Lock type</b>                        | Twist-grip lock with three-point fastening |
| <b>Material</b>                         | Sheet steel                                |
| <b>Colour of front</b>                  | Anthracite grey RAL 7016                   |
| <b>Surface</b>                          | Lacquered                                  |
| <b>Cabinet colour</b>                   | Light grey RAL 7035                        |



### EAN-Code

4251142237649