




Material: Messing vernickelt
 max. Betriebsdruck: 18,0 bar
 verwendbare Schläuche: PA, PE, PU



16.012-8-E

Überwurfmuttern

Artikel Nr.	Ident Nr.	ØD	A	B	
16.007-5-E	115485	5/3	M 7x0,75	8,5	8
16.010-6-E	115486	6/4	M 10x1	10,5	12
16.012-8-E	115487	8/6	M 12x1	10,5	14
16.014-10-E	115488	10/8	M 14x1	11,5	16
16.016-12-E	115489	12/10	M 16x1	13,0	18