

XBO 1600 W XL OFR

XBO Xtreme Life | Xenon short-arc lamps for cinema projection




Product benefits

- Short arc with very high luminance for brighter screen illumination
- Constant color temperature of 6,000 K throughout the entire lamp lifetime
- Easy to maintain
- High arc stability
- Instant light on screen thanks to hot restart function
- Wide dimming range

Product features

- Wattage: 1,200...8,000 W




Product datasheet

Technical data

Electrical data

Nominal wattage	1600.00 W
Lamp voltage	24 V
Nominal current	65.0 A
Lamp current	65.0 A
Current control range	45...75 A

Dimensions & weight



Diameter	52.0 mm
Length	370.0 mm
Length with base excl. base pins/connection	322.00 mm
Light center length (LCL)	143.0 mm ¹⁾
Electrode gap cold	4.8 mm
Cable/wire length, input side	-
Product weight	418.00 g

¹⁾ Distance from end of base to tip of electrode (cold)

Temperatures & operating conditions

Max. permitted ambient temp. pinch point	230 °C
--	--------

Lifespan

Lifespan	3500 h
----------	--------

Additional product data

Base anode (standard designation)	SFaX27-10
Base cathode (standard designation)	SFa27-12

Product datasheet

Capabilities

Cooling	Forced
Burning position	s30 ¹⁾

¹⁾ Anode on top

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4008321299918	OSRXBO1600XL	-	-	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321299918	XBO 1600 W XL OFR	Shipping carton box 1	590 mm x 229 mm x 234 mm	31.62 dm ³	1504.40 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.