



## Griffschrauben, Griffmuttern

Material: PA 6 (SK-01)  
Farben: schwarz




Artikel-Nr.	A	B	C	D	E	VPE Stück
105 0615 699 01	M6	15,0	30,0	16,0	4,0	50
105 0620 699 01	M6	20,0	30,0	16,0	4,0	50
105 0630 699 01	M6	30,0	30,0	16,0	4,0	50
105 0640 699 01	M6	40,0	30,0	16,0	4,0	50
105 0650 699 01	M6	50,0	30,0	16,0	4,0	50
105 0820 699 01	M8	20,0	40,0	20,0	10,0	50
105 0830 699 01	M8	30,0	40,0	20,0	10,0	50
105 0840 699 01	M8	40,0	40,0	20,0	10,0	50
105 0850 699 01	M8	50,0	40,0	20,0	10,0	50
105 0860 699 01	M8	60,0	40,0	20,0	10,0	50
105 1020 699 01	M10	20,0	50,0	20,0	10,0	50
105 1030 699 01	M10	30,0	50,0	20,0	10,0	50
105 1040 699 01	M10	40,0	50,0	20,0	10,0	50
105 1050 699 01	M10	50,0	50,0	20,0	10,0	50
105 1060 699 01	M10	60,0	50,0	20,0	10,0	50




106 0630 699 01	M6	9,0	30,0	16,0	4,0	25
106 0840 699 01	M8	12,0	40,0	20,0	10,0	25
106 1050 699 01	M10	12,0	50,0	20,0	10,0	25

## Kugelknöpfe

Material: Bakelit (SK-15)  
Farbe: schwarz (glänzend)



Artikel-Nr.	A	B	C	D	E	VPE Stück
107 0416 699 15	M4	7,0	16,0	8,0	15,0	50
107 0520 699 15	M5	9,0	20,0	12,0	18,0	50
107 0625 699 15	M6	11,0	25,0	15,0	22,5	50
107 0832 699 15	M8	14,0	32,0	18,0	29,0	10
107 1040 699 15	M10	18,0	40,0	22,0	37,0	10
107 1250 699 15	M12	21,0	50,0	28,0	46,0	10
107 1450 699 15	M14	21,0	50,0	28,0	46,0	10
107 1650 600 15	M16	21,0	50,0	28,0	46,0	10



Abmessungen in mm