

CD 40X40 4/6 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Type	CD 40X40 4/6 GY
Order No.	2589210000
Version	Cable duct, 40 mm x 40 mm, 4.00 mm x 6.00 mm, 2000 mm
GTIN (EAN)	4050118603057
Qty.	40 m

Data sheet

CD 40X40 4/6 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	2,000 mm	Length (inches)	78.74 inch
Width	40 mm	Width (inches)	1.575 inch
Height	40 mm	Height (inches)	1.575 inch
Net weight	328 g		

General information

Colour	grey	Cover	Yes
Flexible wiring duct	No	Halogen	Yes
Material	PVC	Non-tracking	Yes
Slit gap	6 mm	Slit width	4 mm
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	1,310 mm ²	Version of side panel	slotted

Classifications

ETIM 6.0	EC000012	eClass 6.2	27-40-07-03
eClass 9.1	27-40-07-03		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [STEP](#)

Data sheet

CD 40X40 4/6 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

