


**Chain Products, Ropes, Accessories,  
Clamps and Fittings**

**Campbell®**

## Campbell® Table of Contents

Contents	Page No.
Chains	9–12
Ropes	13–14
Tie Downs & Slings	15
Accessories	16–20
Hooks	21–22
Latch Kits for Hooks	23
Swivels	24
Swaging Tool & Ferrules and Stops	25
Lifting Clamps	26–37
Campbell® Numerical Index	201–202

- inside use
- outside use
- stainless steel



Code No.	Description	d x t x b / mm	Reel-Type	m per Reel
<b>Hobby-Chains</b>				
T0120711917	● Forcat-Chain, brass plated	1,1 x 5 x 5	A	25
T0120711927	● Forcat-Chain, nickel plated	1,1 x 5 x 5	A	25
T0120717017	● Gourmante-Chain, brass plated	1,2 x 3,5 x 4	A	25
T0120717027	● Gourmante-Chain, nickel plated	1,2 x 3,5 x 4	A	25
T0120719017	● Gourmante-Chain, brass plated	1,5 x 4 x 5	A	25
T0120719027	● Gourmante-Chain, nickel plated	1,5 x 4 x 5	A	25
T0120712017	● Twist Link Chain, brass plated	2,0 x 8 x 7	A	15
T0120712027	● Twist Link Chain, nickel plated	2,0 x 8 x 7	A	15
T0120712077	● Twist Link Chain, black	2,0 x 8 x 7	A	15
T0120712517	● Twist Link Chain, brass plated	2,5 x 7 x 9	A	10
T0120712527	● Twist Link Chain, nickel plated	2,5 x 7 x 9	A	10
T0120712577	● Twist Link Chain, black	2,5 x 7 x 9	A	10
T0120710317	● Clock-Chain, brass plated	1,1 x 7 x 4,5	A	50
T0120710327	● Clock-Chain, nickel plated	1,1 x 7 x 4,5	A	50
T0120710329	● Clock-Chain, nickel plated	1,1 x 7 x 4,5	A	25
T0120710377	● Clock-Chain, black	1,1 x 7 x 4,5	A	50
T0120710379	● Clock-Chain, black	1,1 x 7 x 4,5	A	25
T0120710387	● Clock-Chain, lead coloured	1,1 x 7 x 4,5	A	50
T0120710397	● Clock-Chain, antique copper	1,1 x 7 x 4,5	A	50
T0120710399	● Clock-Chain, antique brass	1,1 x 7 x 4,5	A	25
T0120710517	● Clock-Chain, brass plated	1,3 x 7,5 x 5	A	25
T0120710527	● Clock-Chain, nickel plated	1,3 x 7,5 x 5	A	25
T0120710717	● Clock-Chain, brass plated	1,6 x 8 x 6	A	25
T0120710727	● Clock-Chain, nickel plated	1,6 x 8 x 6	A	25
T0120710777	● Clock-Chain, black	1,6 x 8 x 6	A	25
T0120710737	● Clock-Chain, lead coloured	1,6 x 8 x 6	A	25
T0120710797	● Clock-Chain, antique brass	1,6 x 8 x 6	A	25
T0120710747	● Clock-Chain, white epoxy coated	1,6 x 8 x 6	A	25
T0120710757	● Clock-Chain, solid brass	1,6 x 8 x 6	A	25
T0120710767	● Clock-Chain, Inox, stainless steel	1,6 x 8 x 6	A	25
T0120711624	● Jack Chain, el. galvanized & blue chromed	1,6	A	20



Forcat-Chain



Gourmante-Chain



Twist Link Chain



Clock-Chain



Jack Chain




Victor Chain

<b>Victor Chains DIN 5686</b>				
T0120710624	● Victor Chain, el. galvanized & blue chromed	1,4 x 20 x 6,5	B	90
T0120710524	● Victor Chain*, el. galvanized & blue chromed	1,6 x 23 x 7	B	60
T0120710424	● Victor Chain*, el. galvanized & blue chromed	1,8 x 26,5 x 8	B	50
T0120710324	● Victor Chain*, el. galvanized & blue chromed	2,0 x 28 x 9	B	50
T0120710224	● Victor Chain, el. galvanized & blue chromed	2,2 x 31 x 10	B	30
T0120710124	● Victor Chain, el. galvanized & blue chromed	2,5 x 35 x 11	B	30
T0120711024	● Victor Chain, el. galvanized & blue chromed	2,8 x 39 x 12,5	B	30
T0120712034	● Victor Chain*, el. galvanized & blue chromed	3,1 x 41 x 14	B	20
T0120713524	● Victor Chain, el. galvanized & blue chromed	3,4 x 44 x 15,5	B	15
T0120710284	● Victor Chain, white epoxy coated	2,2 x 31 x 10	B	30
T0120710294	● Victor Chain, pink epoxy coated	2,2 x 31 x 10	B	30
T0120710295	● Victor Chain, turquoise epoxy coated	2,2 x 31 x 10	B	30
T0120710494	● Victor Chain, Inox, stainless steel	1,8 x 28 x 9	B	60

### Assorted Chains

- outside use
- stainless steel



Sash-Chain



Ball-Chain



C-Link Chain



A-Link Chain



C-Link Chain



Calibrated Chain



Plastic Chain

Code No.	Description	d x t x b / mm	Reel- Type	m per Reel	Working load limit kg **
<b>Sanitary Chains</b>					
T0120710127	● Sash-Chain, solid brass, nickel plated	0,3 x 10,5 x 4	A	50	-
T0120710217	● Sash-Chain, solid brass	0,4 x 12,5 x 5	A	50	-
T0120710227	● Sash-Chain, solid brass, nickel plated	0,4 x 12,5 x 5	A	50	-
T0120713017	● Sash-Chain, solid brass	0,5 x 19,5 x 7	A	25	-
T0120713027	● Sash-Chain, solid brass, nickel plated	0,5 x 19,5 x 7	A	25	-
T0120712617	● Ball-Chain, solid brass, nickel plated	2,5	A	100	-
T0120713627	● Ball-Chain, solid brass, nickel plated	3,6	A	25	-
T0120713617	● Ball-Chain, solid brass	4,5	A	25	-

#### Welded round link chains, form C long links, el. galvanized and blue chromed, DIN 5685

T0120332007	● C-Link Chain*	2,0 x 22 x 8	B	60	30
T0120333007	● C-Link Chain*	3,0 x 26 x 12	C	60	70
T0120334007	● C-Link Chain*	4,0 x 32 x 16	C	58	125
T0120335007	● C-Link Chain*	5,0 x 35 x 20	C	32	195
T0120336007	● C-Link Chain*	6,0 x 42 x 24	C	28	290
T0120337007	● C-Link Chain*	7,0 x 48 x 28	C	26	375
T0120338007	● C-Link Chain*	8,0 x 52 x 32	C	20	500

(\*also available in 30 m bundles)

#### Welded round link chains, form A short links, el. galvanized and blue chromed, DIN 5685

T0120313027	● A-Link Chain*	2,0 x 12 x 8	B	60	30
T0120313037	● A-Link Chain*	3,0 x 16 x 12	C	100	70
T0120313047	● A-Link Chain*	4,0 x 19 x 16	C	50	125
T0120313057	● A-Link Chain*	5,0 x 21 x 20	C	35	195
T0120313067	● A-Link Chain*	6,0 x 24 x 24	C	35	290
T0120313087	● A-Link Chain*	8,0 x 32 x 32	C	20	500
T0120313107	● A-Link Chain	10,0 x 40 x 37	C	10	630

(\*also available in 30 m bundles)

#### Welded round link chains, form C, stainless steel, Inox 316, DIN 5685

T0120192007	● C-Link Chain, Inox	2,0 x 22 x 8	B	30	30
T0120193007	● C-Link Chain, Inox	3,0 x 26 x 12	B	25	70
T0120194007	● C-Link Chain, Inox	4,0 x 32 x 16	B	20	125
T0120195007	● C-Link Chain, Inox	5,0 x 35 x 20	B	15	195

#### Calibrated round link chains, el. galvanized and blue chromed, DIN 766

T0120147665	● Calibrated Chain	5,0 x 18,5 x 17	C	40	250
-------------	--------------------	-----------------	---	----	-----

#### Plastic Chains, Polyethylene


T0120992007	● Plastic Chain, yellow/black	6,0 x 40 x 22	C	25	-
T0120993007	● Plastic Chain, red/white	6,0 x 40 x 22	C	25	-
T0120994007	● Plastic Chain, white	6,0 x 40 x 22	C	25	-
T0120995007	● Plastic Chain, black	6,0 x 40 x 22	C	25	-
T0120997007	● Plastic Chain, copper coloured	6,0 x 40 x 22	C	25	-
T0120991207	● Plastic Chain, yellow/black	8,0 x 48 x 26	C	25	-
T0120991807	● Plastic Chain, red/white	8,0 x 48 x 26	C	25	-
T0120998007	● Plastic Chain, black	10,0 x 61 x 33	C	12,5	-
T0120999007	● Plastic Chain, copper coloured	10,0 x 61 x 33	C	12,5	-

\*\* Specifications on the working load limit only for A and C formed chains



Assorted Chains

- inside use
- outside use
- stainless steel



Code No.	Description	d x t x b / mm	Reel-Type	m per Reel
<b>Round link chains form C long links</b>				
T0120996060	● C-Link Chain, galvanized & red/white epoxy coated	6,0 x 42 x 24	C	25



C-Link Chain

<b>Deco- and Lamp-Chains</b>				
T0120711017	● Deco-Chain round, brass plated	2,0 x 15 x 10	B	50
T0120711077	● Deco-Chain round, black	2,0 x 15 x 10	B	50
T0120711027	● Deco-Chain round, nickel plated	2,0 x 15 x 10	B	50
T0120711097	● Deco-Chain round, burnished	2,0 x 15 x 10	B	50
T0120711087	● Deco-Chain round, white epoxy coated	2,0 x 15 x 10	B	50
T0120711317	● Deco-Chain round, brass plated	2,8 x 19 x 15	B	30
T0120711377	● Deco-Chain round, black	2,8 x 19 x 15	B	30
T0120711327	● Deco-Chain round, nickel plated	2,8 x 19 x 15	B	30
T0120711387	● Deco-Chain round, white epoxy coated	2,8 x 19 x 15	B	30
T0120711314	● Deco-Chain round, solid brass	2,8 x 19 x 15	B	30
T0120710097	● Deco-Chain round, antique brass	2,8 x 19 x 15	B	30
T0120714017	● Deco-Chain squared, brass plated	2,0 x 16 x 9	B	50
T0120714077	● Deco-Chain squared, black	2,0 x 16 x 9	B	50
T0120714097	● Deco-Chain squared, burnished	2,0 x 16 x 9	B	50
T0120715017	● Deco-Chain squared, brass plated	3,0 x 29 x 14	B	20
T0120715077	● Deco-Chain squared, black	3,0 x 29 x 14	B	20
T0120715097	● Deco-Chain squared, burnished	3,0 x 29 x 14	B	20
T0120715087	● Deco-Chain squared, white epoxy coated	3,0 x 29 x 14	B	20
T0120716077	● Deco-Chain squared, black	4,0 x 29 x 17	B	20
T0120717217	● Deco-Chain squared, twisted, brass plated	3,5 x 37 x 20	B	20
T0120717277	● Deco-Chain squared, twisted, black	3,5 x 37 x 20	B	20
T0120715297	● Deco-Chain squared, twisted, antique brass	3,5 x 37 x 20	B	20
T0120717297	● Deco-Chain squared, twisted, burnished	3,5 x 37 x 20	B	20
T0120713117	● Deco-Chain cathedral, brass plated	2,2 x 24 x 15	B	30
T0120713177	● Deco-Chain cathedral, black	2,2 x 24 x 15	B	30
T0120713197	● Deco-Chain cathedral, burnished	2,2 x 24 x 15	B	30
T0120713217	● Deco-Chain cathedral, brass plated	2,8 x 39 x 20	B	20
T0120713277	● Deco-Chain cathedral, black	2,8 x 39 x 20	B	20
T0120713297	● Deco-Chain cathedral, burnished	2,8 x 39 x 20	B	20
T0120713267	● Deco-Chain cathedral, antique brass	2,8 x 39 x 20	B	20



Deco-Chain round



Deco-Chain squared



Deco-Chain twisted



Deco-Chain cathedral

Code No.	Description	d x Length	📦
<b>Security Chains, round links, 60 HRC case hardened</b>			
0122101506	Security Chain, el. galvanized, polycoated blue	5,0 x 600	5
0122101509	Security Chain, el. galvanized, polycoated blue	5,0 x 900	5
0122101512	Security Chain, el. galvanized, polycoated blue	5,0 x 1200	5
0122101709	Security Chain, el. galvanized, polycoated blue	7,0 x 900	5
0122101715	Security Chain, el. galvanized, polycoated blue	7,0 x 1500	2
0122102712	Top Security Chain with squared links, el. galvanized with poly sleeve	7,0 x 1200	5
0122102112	Top Security Chain with squared links, el. galvanized with poly sleeve	10,0 x 1200	2




Security Chain, round links



Top Security Chain with squared links

### Chains in Bundles

- outside use
- stainless steel




Victor chain



C-link chain



A-link chain



Plastic chain

Code No.	Description	d x t x b /mmm per Bundle	Working load limit kg **
<b>Victor chains, el. galvanized and blue chromed, DIN 5686</b>			
T0120719524	● Victor chain	1,6 x 23 x 7	30
T0120719424	● Victor chain	1,8 x 26,5 x 8	30
T0120719324	● Victor chain	2,0 x 28 x 9	30
T0120719224	● Victor chain	2,2 x 31 x 10	30
T0120719124	● Victor chain	2,5 x 35 x 11	30
T0120719024	● Victor chain	2,8 x 39 x 12,5	30
T0120719034	● Victor chain	3,1 x 41 x 14	30

<b>Welded round link chains, form C long links, el. galvanized and blue chromed, DIN 5685</b>				
T0120332097	● C-link chain	2,0 x 22 x 8	30	30
T0120333097	● C-link chain	3,0 x 26 x 12	30	70
T0120334097	● C-link chain	4,0 x 32 x 16	30	125
T0120335097	● C-link chain	5,0 x 35 x 20	30	195
T0120336097	● C-link chain	6,0 x 42 x 24	30	290
T0120337097	● C-link chain	7,0 x 48 x 28	30	375
T0120338097	● C-link chain	8,0 x 52 x 32	30	500

<b>Welded round link chains, form A short links, el. galvanized and blue chromed, DIN 5685</b>				
T0120313927	● A-link chain	2,0 x 12 x 8	30	30
T0120313937	● A-link chain	3,0 x 16 x 12	30	70
T0120313947	● A-link chain	4,0 x 19 x 16	30	125
T0120313957	● A-link chain	5,0 x 21 x 20	30	195
T0120313967	● A-link chain	6,0 x 24 x 24	30	290
T0120313987	● A-link chain	8,0 x 32 x 32	30	500

<b>Plastic chains, Polyethylene</b>				
T0120992097	● Plastic chain, yellow/black	6,0 x 40 x 22	25	-
T0120993097	● Plastic chain, red/white	6,0 x 40 x 22	25	-

<b>Welded round link chains, form C, straight, long links, fire galvanized, DIN 5685</b>				
T0120333197	● C30 C-link chain	3,0 x 26 x 12	30	70
T0120335197	● C50 C-link chain	5,0 x 35 x 20	30	195
T0120336197	● C60 C-link chain	6,0 x 42 x 24	30	290
T0120338197	● C80 C-link chain	8,0 x 52 x 32	30	500

<b>Welded round link chains, form C, straight, long links, INOX stainless steel, DIN 5685</b>				
T0120194107	● C40 C-link chain	4,0 x 32 x 16	30	125

\*\* Specifications on the working load limit only for A and C formed chains

- Natural ropes
- Universal ropes

Code No.	Description	Diameter mm	Reel-Type	m per Reel	Working load limit kg
<b>Sisal-Ropes</b>					
T0120980560	● Sisal-Rope twisted, natural	6,0	D	60	–
T0120980580	● Sisal-Rope twisted, natural	8,0	E	120	–
T0120980500	● Sisal-Rope twisted, natural	10,0	E	70	–

<b>Braided Twines</b>					
T0120980630	● Braided Twine PP-multifil, white	3,0	D	450	60
T0120980631	● Braided Twine PP-multifil, yellow	3,0	D	450	60
T0120980633*	● Braided Twine PP-multifil, pink	3,0	D	450	60
T0120980634	● Braided Twine PP-multifil, red	3,0	D	450	60
T0120980635	● Braided Twine PP-multifil, mint	3,0	D	450	60
T0120980636	● Braided Twine PP-multifil, green	3,0	D	450	60
T0120980637	● Braided Twine PP-multifil, blue	3,0	D	450	60
T0120980638	● Braided Twine PP-multifil, brown	3,0	D	450	60
T0120980639	● Braided Twine PP-multifil, black	3,0	D	450	60
T0120980640	● Braided Rope PP-multifil, white	4,0	D	180	180
T0120980650	● Braided Rope PP-multifil, white	5,0	D	120	240
T0120980660	● Braided Rope PP-multifil, white	6,0	D	100	380
T0120980661	● Braided Rope PP-multifil, yellow	6,0	D	100	380
T0120980662	● Braided Rope PP-multifil, red	6,0	D	100	380
T0120980665	● Braided Rope PP-multifil, green	6,0	D	100	380
T0120980666	● Braided Rope PP-multifil, blue	6,0	D	100	380
T0120980680	● Braided Rope PP-multifil, white	8,0	E	120	550
T0120980682	● Braided Rope PP-multifil, red	8,0	E	120	550
T0120980683	● Braided Rope PP-multifil, blue	8,0	E	120	550
T0120980685	● Braided Rope PP-multifil, mint	8,0	E	120	550
T0120980686	● Braided Rope PP-multifil, red/green	8,0	E	120	550

\* Discontinued, while quantity lasts

<b>PP-Ropes</b>					
T0120980761	● PP-Rope twisted, orange	6,0	D	60	380
T0120980780	● PP-Rope twisted, orange	8,0	E	120	800
T0120980700	● PP-Rope twisted, orange	10,0	E	70	1350

<b>Nylon and Spleitex-Ropes</b>					
T0120980860	● Nylon-Rope twisted, white	6,0	D	60	700
T0120980880	● Nylon-Rope twisted, white	8,0	E	120	1100
T0120980800	● Nylon-Rope twisted, white	10,0	E	70	1700
T0120980060	● Spleitex-Rope twisted, hemp coloured	6,0	D	60	290
T0120980000	● Spleitex-Rope twisted, hemp coloured	10,0	E	70	800

<b>Sailing-Ropes</b>					
T0120980100	● Sailing-Rope double braided, white/red	10,0	E	70	800

<b>Jalousietwines</b>					
T0120980220	● Jalousietwine, 16 x braided, white	2,2	D	500	120
T0120980230	● Jalousietwine, 16 x braided, white	3,0	D	300	150

Code No.	Description	Diameter mm	Reel-Type	m per Reel	min. breaking strength*
<b>Wire-Ropes, according DIN EN 12385-4</b>					
T0120981520	● Wire rope cable el. galvanized	2,0	D	153	2.35
T0120981530	● Wire rope cable el. galvanized	3,0	D	153	5.29
T0120981540	● Wire rope cable el. galvanized	4,0	D	100	9.41
T0120981620	● Wire rope cable el. galvanized PVC coated	2,0/3,0	D	153	2.35
T0120981630	● Wire rope cable el. galvanized PVC coated	3,0/4,5	D	100	5.29

\* in Kilo Newton – kN; (10 Newton = 1 kg)



Sisal-Rope



Braided Twines & Ropes



PP-Rope



Nylon-Rope



Spleitex-Rope



Sailing-Rope



Jalousietwine



Wire-Rope

### Assorted Prepacked Ropes

- Natural ropes
- Universal ropes



Code No.	Description	Diameter mm	Length m		
<b>Hasps</b>					
T0120986830	● Braided Nylon Twine, white	3,5	20	Hasp	5
T0120986901	● Blocking Tape PP 80 mm, red/white	–	50	Hasp	5
T0120986560	● Sisal Rope twisted, natural	6,0	20	Hasp	5
T0120986580*	● Sisal Rope twisted, natural	8,0	10	Hasp	5
T0120986660	● PP-Rope braided, blue/red	6,0	20	Hasp	5
T0120986860	● PA-Rope twisted, white	6,0	20	Hasp	5

\* Discontinued, while quantity lasts



<b>Balls</b>					
T0120987800	● Poly Packing Twine, assorted colours	1,0	80	Ball	10
T0120987801	● Twiny-Twine (2 Balls)	2,0/1,0	10/30	Ball	10
T0120987410	● Hemp-Twine 50 g	0,9	35	Ball	10



<b>Skeins</b>					
T0120988840	● Universal Rope, white	4,8	15	Skein	10
T0120988740	● All Purpose Rope, assorted colours	4,0	9	Skein	10
T0120988850	● Synthetic Laundry Twine & 1 Hook	5,0	20	Skein	10
T0120988580	● Sisal Rope twisted	8,0	15	Skein	5
T0120988780	● All Purpose Rope, orange	8,0	25	Skein	5
T0120988160	● PP-Boat Rope, twisted & Snaphook, orange	6,0	8	Skein	5
T0120988781	● All Purpose PP-Rope, orange	8,0	20	Skein	5
T0120988700	● All Purpose PP-Rope, orange	10,0	25	Skein	5
T0120988704	● PP-Rope twisted, black/white	14,0	10	Skein	5



<b>Ring</b>					
T0120989500	● Sisal rope	10,0	10	Ring	10



**Tie Downs & Slings**

Tie & Lift 100% Polyester belts, Tie downs DIN EN12195-2 / Slings DIN 61360

Code No.	Description	Load Limit kg	Width mm	Length m	☐
<b>Tie down up to 250 kg (prepacked)</b>					
T0120982000	Cam Buckle Tie Down, blue (2 pcs.)	250	25	3	5
T0120982001	Cam Buckle Tie Down, blue	250	25	5	5



<b>Tie down up to 250 kg (bulk)</b>					
T0120982700	Cam Buckle Tie Down, blue	250	25	3	5
T0120982701	Cam Buckle Tie Down, blue	250	25	5	5

<b>Tie down up to 500 kg (prepacked)</b>					
T0120982010	Ratchet Tie Down, one part, orange	500	25	5	5
T0120982011	Ratchet Tie Down & Hook, two part, orange	500	25	5	5



<b>Tie down up to 500 kg (bulk)</b>					
T0120982710	Ratchet Tie Down, one part, orange	500	25	5	5
T0120982711	Ratchet Tie Down & Hook, two part, orange	500	25	5	5

<b>Tie down up to 2.000 kg (prepacked)</b>					
T0120982020	Ratchet Tie Down, one part, violet	2.000	35	6	5
T0120982021	Ratchet Tie Down & Hook, two part, violet	2.000	35	6	5



<b>Tie down up to 2.000 kg (bulk)</b>					
T0120982720	Ratchet Tie Down, one part, violet	2.000	35	6	5
T0120982721	Ratchet Tie Down & Hook, two part, violet	2.000	35	6	5

<b>Tie down up to 3.000 kg (prepacked)</b>					
T0120982031	Ratchet Tie Down & Hook, two part, yellow	3.000	50	8	2



<b>Tie down up to 3.000 kg (bulk)</b>					
T0120982730	Ratchet Tie Down, one part, yellow	3.000	50	8	2
T0120982731	Ratchet Tie Down & Hook, two part, yellow	3.000	50	8	2

Code No.	Description	Capacity kg	Length m	☐
<b>Round Slings up to 1.000 kg (prepacked)</b>				
T0120982050	Round Sling, violet	1.000	3	5

<b>Round Slings up to 1.000 kg (bulk)</b>				
T0120982750	Round Sling, violet	1.000	3	5



## Prepacked Accessories



Code No.	Description	Diameter mm	Pcs./Card	
<b>Welded Rings (prepacked)</b>				
T0120983502	Welded ring, round, el. galv., 25 mm	4,0	2	10
T0120983503	Welded ring, round, el. galv., 40 mm	5,0	1	10



Code No.	Description	Diameter mm	Pcs./Polybag	
<b>Welded Rings (bulk)</b>				
T0120984502	Welded ring, round, el. galv., 25 mm	4,0	100	
T0120984503	Welded ring, round, el. galv., 40 mm	5,0	100	

Code No.	Description	Diameter mm	Pcs./Card	
<b>Rope shortening &amp; Blocking (prepacked)</b>				
T0120983511	Rope shortening & blocking, el. galvanized	5,4	1	10



Code No.	Description	Length mm	Pcs./Polybag	
<b>Simplex Snap Hooks (bulk)</b>				
T0120984524	Simplex snap hook, el. galvanized	30,0	100	
T0120984525	Simplex snap hook, el. galvanized	40,0	100	



Code No.	Description	Diameter mm	Pcs./Card	
<b>S-Hooks (prepacked)</b>				
T0120983540	S-Hook, el. galvanized	2,5	2	10
T0120983541 *	S-Hook, el. galvanized	3,0	2	10
T0120983542	S-Hook, el. galvanized	4,0	2	10
T0120983543	S-Hook, el. galvanized	5,0	2	10
T0120983544	S-Hook, el. galvanized	6,0	2	10

\* Discontinued, while quantity lasts

Code No.	Description	Diameter mm	Pcs./Polybag	
<b>S-Hooks (bulk)</b>				
T0120984540	S-Hook, el. galvanized	2,5	100	
T0120984541	S-Hook, el. galvanized	3,0	100	
T0120984542	S-Hook, el. galvanized	4,0	100	
T0120984543	S-Hook, el. galvanized	5,0	100	
T0120984544	S-Hook, el. galvanized	6,0	100	

**Prepacked Accessories**

Code No.	Description	Diameter mm	Pcs./Polybag	☐
<b>Connecting Links (bulk)</b>				
T0120984561	Connecting link, el. galvanized	4,0	100	
T0120984562	Connecting link, el. galvanized	5,0	100	
T0120984563	Connecting link, el. galvanized	6,0	100	



Code No.	Description	Diameter mm	Pcs./Card	☐
<b>Snap Hooks (prepacked)</b>				
T0120983582	Alu.-Snap hook & key ring, assorted colours	6,0	1	10

Code No.	Description	Diameter mm	Pcs./Polybag	☐
<b>Snap Hooks (bulk)</b>				
T0120984582	Alu.-Snap hook & key ring, assorted colours	6,0	25	



Code No.	Description	Diameter mm	Pcs./Card	
<b>Wire Rope Clips (prepacked)</b>				
T0120983590	Wire rope clips, el. galvanized	3,0	2	10
T0120983591	Wire rope clips, el. galvanized	5,0	2	10

Code No.	Description	Diameter mm	Pcs./Polybag	☐
<b>Wire Rope Clips (bulk)</b>				
T0120984590	Wire rope clips, el. galvanized	3,0	100	
T0120984591	Wire rope clips, el. galvanized	5,0	100	



Code No.	Description	Diameter mm	Pcs./Card	☐
<b>Single and Double Clamps (prepacked)</b>				
T0120983610	Simplex clamp, el. galvanized	3,0	2	10
T0120983611	Simplex clamp, el. galvanized	5,0	2	10
T0120983612	Duplex clamp, el. galvanized	3,0	2	10
T0120983613	Duplex clamp, el. galvanized	5,0	1	10



Code No.	Description	Diameter mm	Pcs./Polybag	☐
<b>Single and Double Clamps (bulk)</b>				
T0120984610	Simplex clamp, el. galvanized	3,0	100	
T0120984611	Simplex clamp, el. galvanized	5,0	100	
T0120984612	Duplex clamp, el. galvanized	3,0	100	
T0120984613	Duplex clamp, el. galvanized	5,0	100	

