

# PC 153410



Sample image

**Order symbol:** PC 153410

**Product nbr:** 7032700

UL Code: 7042700

UL Name: UL PC 153410

**Description:** Enclosure. PC


**Remarks:** Opaque cover

**Including:** Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.

**EAN:** 6418074058447

**El. number:**

- Finland: 3435368
- Denmark: 8212004359
- Sweden: 2536141



**Dimensions:**

|       | Height | Width | Depth |
|-------|--------|-------|-------|
| mm:   | 150    | 340   | 100   |
| inch: | 5.91   | 13.39 | 3.94  |

**Materials:**

|                  |                      |
|------------------|----------------------|
| Material:        | Polycarbonate        |
| Base colour:     | RAL 7035 -light grey |
| Cover colour:    | RAL 7035 -light grey |
| Gasket material: | Polyurethane         |

**Temperatures:**

|                              |             |
|------------------------------|-------------|
| Temperature °C (short term): | -40 ... 120 |
| Temperature °C (continuous): | -40 ... 80  |
| Temperature °F (short term): | -40 ... 250 |
| Temperature °F (continuous): | -40 ... 175 |

**Accessories:**

|          |   |
|----------|---|
| TRH 34   | DIN-15 Mounting rail. for enclosures:<br>(307 x 35 x 1) |
| TF 28037 | Mounting foot kit (4 pcs). for enclosures:              |
| TRH 15   | DIN-15 Mounting rail. for enclosures:<br>(122 x 35 x 1) |
| TM 1534  | Back Panel. for enclosures:<br>(303 x 136 x 1)          |
| TH A     | Gray plastic hinges (2 pcs)                             |

**Rating:**

|  |                   |
|--|-------------------|
| Ingress protection (EN 60529):         | IP66; IP67;       |
| Impact Resistance (EN 62262):          | IK07; IK08;       |
| Electrical insulation:                 | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815): | 1                 |
| UV resistance:                         | UL 508            |
| Flammability Rating:                   | UL 746C 5*        |
| Glow Wire Test (IEC 695-2-1) °C:       | 960 °C            |
| NEMA Class                             |                   |

**Certificates:**

SGSFimko\_EURONORD