

## Product information

# 76 22 125

## Diagonal Cutter

For electromechanics

DIN ISO 5749

- With sharp, precisely aligned cutting edges
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- Lap joint
- Without bevel for flush cutting of soft wires
- Vanadium electric steel, forged, multi stage oil-hardened




### General

Article No.	76 22 125
EAN	4003773048022
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	107 g
Dimensions	125 x 57 x 19 mm
Standard	DIN ISO 5749
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities soft wire (diameter)	Ø 0.4 – 2.5 mm
Jaw length (B)	16 mm
Jaw thickness (joint) (D)	9 mm
Head width (A)	14.5 mm



*technical change and errors excepted*