

Part # 901, 30 AWG (Solid) Silver Plated Copper Wire Kynar Insulated UL Style 1423, Consolidated Hook Up Wire

Product Construction
Conductor:

- 30 AWG (Solid) Silver Plated Copper Wire Conductor OFHC

Insulation:

- (900 series) color coded Kynar insulation
Temperature -40°C to +105°C

Applications:

- Hook-Up wire
- Point to point wiring
- Printed circuit board wiring

Industry Approvals:

- UL Style 1423
- RoHS Compliant

Packaging:

- 1000 ft. spools
- 100 ft. spools
- Also available on bulk reels

Note: KYNAR® (PVDF Polyvinylidene Fluoride) is a trademark of Pennwalt Corp.



Specifications

Gauge	30 AWG
Strands	(Solid) Silver Plated Copper Wire
Insulation Type	Kynar
Nominal Insulation Wall	0.004 in.
Nominal O.D.	0.020 in.
Color	0-Black/1-Brown/2-Red/3-Orange/4-Yellow/5-Green/6-Blue/7-Violet/8-Gray/9-White
Color Code Chart	Chart-Hook-Up Wire
UL Style	1423
Insulation Temperature	-40 to +105 °C