



Datenblatt - Fiche technique - Data sheet

11.09.4385




ROLINE Fiber-Kabel Toslink ST / ST, 5m


ROLINE Câble Toslink M/M, 5m

ROLINE Fiber Cable Toslink M - M, 5 m

1. DIMENSION



CORD SPEC.



d1... CORE DIAMETER	φ 0.98mm
d2... CLAD DIAMETER	φ 1.0mm
D1... PRIMARY JACKET DIAMETER	φ 2.2±0.07mm
D2... SECOND JACKET DIAMETER	φ 4.0±0.2mm

NOTE:

1. 100 % TESTING.
2. TRANSMISSION LOSS 4.0 dB (L=10M) OR LESS
3. MATING FORCE :39.2N(4.0Kgf) OR LESS
4. UMATING FORCE :5.9N(0.6Kgf) ~39.2N (4.0Kgf)
5. ALL DIMENSION ARE IN MILLIMETERS.
6. ALL MATERIAL ARE RoHS COMPLIANT.

RoHS COMPLIANT

PART LISTS

NO	DESCRIPTION	MATERIAL	Q'TY	COLOR.FINISHED
1	OPTICAL FIBER CABLE	PVC	1	PANTONE BLACK C
2	OPT PLUG CAP	PVC	2	PANTONE BLACK C
3	TOSLINK OPT PLUG	PBT+G30%	1	PANTONE BLACK C
4	CENTER PIN	BRASS	1	24K GOLD PLATED
5	PROTECTIVE CAP	PVC	2	TRANSPARENT

REV : 1

△					FINISH		Rotronic Co., Ltd PART NO 11.09.4385 11.09.4389 DESCRIPTION. ROLINE Toslink Cable M-M, 5.0m & 10.0m DRAWN NO. SHEET 1/1
△					COLOR		
△					WORKING		
△					PROCESS		
△					MATERIAL		
MARK	REVISION	DATE	SIGN	APPO	TOLERANCE		
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY		SCALE		
		SHEU	SHEU		UNT	mm	
		2012-06-15	2012-06-15				