

HSSE PM roughing cutter

4 cutters, TiAlN-coated

ORION[®]

Application:

Roughing cutter for universal machining.

Execution:

- HSSE PM
- Roughing teeth
- Centre cutting
- TiAlN-coating for maximum service life
- Straight shank according to DIN 1835 B
- Type NR



Art. no.	15906 080
Brand	ORION
Manufacturer Part Number	15906080
Cutting material	HSSE-PM
Surface	TiAlN
Type	NR
Number of cutting edges	4 PCS
Twist angle	30°
Edge protection chamfer length	0.1 mm
Tool holding device	HB parallel shank
Construction length	Long
Cutting edge diameter	8 mm
Cutting edge length	38 mm
Length	88 mm
Shank diameter	10 mm
fz steel 700	0.068 mm
Gross Weight	0.045 kg
Product Group	106

EAN

403924759860 1