

Micrometer

With flat measuring faces and deep throat

Mitutoyo

Application:

For measuring e.g. sheet thickness

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Spherical anvil and flat spindle
- Friction coupling for consistent, repeatable measuring force

Advantage:

- Micrometer with deep throat

Delivery:

Including box, adjustment wrench, setting standard (from 25 mm)



Art. no.	32016 471
Brand	MITUTOYO
Manufacturer Part Number	118-110
Min./max. length measuring range	25-50 mm
Vernier scale	0.01 mm
Measuring surface diameter	6.3 mm
Measuring spindle increments	0.5 mm
Bracket depth	165 mm
Spindle clamping	Yes
Error limit	4 µm
Display	Nonius
Type	A – flat/flat
Min./max. measurement force	3-8 N
Calibration Group	D
Gross Weight	1.315 kg
Product Group	3MA

EAN

4946368011882