

Electronic outside micrometer

With ballasted spindle and/or anvil

Mitutoyo

Application:

For measuring curved surfaces and wall thicknesses of pipes, bearings, rings etc.

Execution:

- carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65
- Digimatic

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, set standard (25 mm or more), adjustment wrench, battery



Art. no.	32017 563
Brand	MITUTOYO
Manufacturer Part Number	395-25 1-30
Display	Digital
Min./max. length measuring range	0-25 mm
Digit increment	0.001 mm
Measuring surface diameter	6.3 mm
Measuring arrangement	Spherical (SR4), Plan
Material of measuring bolt	Carbide
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Hold-function (AE lock), Automatic switch-off
Min./max. measurement force	5-10 N
Error limit	2 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	25 mm
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	0.480 kg
Product Group	3MA

EAN

4946368689302