

Drill BE 650

Small and handy drill (650 W, 1 speed)

metabo[®]

Version:

- Spindle with hexagon socket for working with screwdriver bits without a drill chuck
- With adjusting wheel for pre-selecting the rotation speed
- With Vario (V) electronics for working with rotation speeds suitable for the material



Art. no.	7005 022
Model	BE 650
Manufacturer Article Number	600741850
Nominal voltage	230 V
Max. drilling diameter in steel	13 mm
Max. drilling diameter in wood	30 mm
Power input	650 W
Power output	320 W
Idle speed 1st gear min./max.	0-1500 rpm
Cable length	2.5 m
Min./max. drill chuck span width	1.5-13 mm
Weight	1.8 kg
With speed control	Yes
With rubber-coated handle	Yes
With overload protection	No
With restart protection	No
With right/left-hand rotation	Yes
With electronic feedback	Yes
With impulse function	No

EAN-Code

4061792201644