

## SENCITY® OCCHIO 4x4 MIMO Antenna 1399.32.0014

### Description

SENCITY Occhio MIMO 4x4 DAS (Distributed Antenna System) or small cell antenna. It offers 5G coverage, a simple, time-saving installation process and an attractive industry preferred design with a small form factor. Thanks to its multiband capability between 1.7-6 GHz it supports today's and future wireless applications. Antenna includes cable assemblies: SUCOFORM\_122\_LA Plenum cable with Nex10 male (antenna side) and 4.3-10 male (network connection side).



### Product Configuration

### Technical Data

#### Electrical Data

	Band 1	Band 2	Band 3	Band 4
Frequency (MHz)	1695 - 2690	3300 - 4200	4500 - 5000	5150 - 6000
VSWR	1.5	1.5	1.5	1.5
Impedance (Ohm)	50	50	50	50
Gain (dBi)	4	4.5	6.5	6.5
Ambient temperature (°C)				
Port Isolation (dB)	18	22	25	25

#### Ports

	Port 1	Port 2	Port 3	Port 4
Connector	NEX10, jack (female)	NEX10, jack (female)	NEX10, jack (female)	NEX10, jack (female)
Cable Type	SUCOFORM_122_LA_CU_CMP	SUCOFORM_122_LA_CU_CMP	SUCOFORM_122_LA_CU_CMP	SUCOFORM_122_LA_CU_CMP
Polarization	vertical	vertical	vertical	vertical
DC grounded	No	No	No	No

#### Connections

	Band 1	Band 2	Band 3	Band 4
Port 1	X	X	X	X
Port 2	X	X	X	X
Port 3	X	X	X	X
Port 4	X	X	X	X

#### General Data

IMD level -153 dBc at carrier power 2x 43dBm

VSWR 1:1.7 in 1.695-1.8 GHz typical

#### Mechanical Data

Dimensions (mm) 32 x 200 (Height x Diameter)

#### Environmental Data

Environmental conditions indoor  
 Operation temperature (°C) 0 to 55  
 Storage temperature (°C) -40 to 85  
 Transport temperature (°C) -40 to 85  
 Flammability rating UL 94-V0  
 Solar radiation UL 746C, F1

## SENCITY® OCCHIO 4x4 MIMO Antenna 1399.32.0014

2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
Lead-free soldered	yes
REACH 1907/2006/EC	compliant

### Material Data

Radome colour	white
Back plate/base plate colour	black

### Related Products

### Related Documents

Mounting instruction	DOC-0000868068
Outline drawing	DOU-00390805