



|                                |                              |
|--------------------------------|------------------------------|
| Polarized to PCB               | Yes                          |
| Stackable                      | No                           |
| Surface Mount Compatible (SMC) | Yes                          |
| Temperature Range - Operating  | -40° to +105°C               |
| Termination Interface: Style   | Through Hole - Compliant Pin |

**Electrical**

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 30.0A            |
| Grounding to PCB              | No               |
| Voltage - Maximum             | 250V AC (RMS)/DC |

**Material Info****Reference - Drawing Numbers**

|                           |                    |
|---------------------------|--------------------|
| Application Specification | AS-46114-001-001   |
| Packaging Specification   | PK-46114-003-001   |
| Product Specification     | PS-46114-001-001   |
| Sales Drawing             | SD-46114-200-001   |
| Symbol/Footprint Data     | SYM-46114-2360-001 |

This document was generated on 01/05/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**