

FEATURES

- Impedance protected shaded pole motor
- Smooth and efficient air flow
- PBT UL94V-0 thermoplastic impeller
- ideal for industrial applications

RS PRO, 230 V ac, AC Axial Fan, 172 x 150mm, 399.3m³/h, 35W

RS Stock No.: 619-6898



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Brought to you by RS PRO, a range of AC dual ball bearing axial fans offering a cost effective cooling solution without sacrificing on quality or reliability. Provided are a robust die-cast aluminium frame and an AC shaded pole impedance protected motor, these fans are ideal for a multitude of applications. All models are highly reliable and excellent quality.

General Specifications

Air Flow	235CFM
Fan Speed	3500rpm
Noise Level	55dB
Direction of Curve	Forward
Frame	Die Cast Aluminium
Impeller	PBT UL94V-0 Plastic
Alarm Function	No
IP Rating	IP44
Applications	Server racks, Electrical cabinets and enclosures; Production Lines, Ceiling fan/ventilation Desktop computers, Motor engines (radiator in a car), Generators, Air compressors

Electrical Specifications

AC or DC Operation	AC
Power Consumption	35W
Supply Voltage	230VAC
Maximum Current	150mA
Frequency in Hz	50/60
Dielectric Strength	1 minute @ 1500 VAC, 50/60 Hz

Mechanical Specifications

Dimensions	172mm x 150mm
Height	172mm
Width	150mm
Depth	51mm
Bearing Type	Ball
Life Expectancy	60,000 hours (L10)

Operation Environment Specifications

Operating Temperature	-10°C to 70°C
------------------------------	---------------

Approvals

Compliance/Certifications	UL, cUL, TUV, CE, UL94-V0
----------------------------------	---------------------------



Dimensions: (mm)

