


AC2251

AS-Interface control cabinet module

SmartL25 4DI 4DO T C



1 addressing socket



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	250
Max. current load total	[A]	4; (> 50 °C: 2000 mA)
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4; Number of digital outputs: 4
------------------------------	---

Inputs

Number of digital inputs	4
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Voltage supply	[V] 18...30
Max. total current rating of inputs	[mA] 200
Input current High	[mA] 6...10
Input current Low	[mA] 0...2
Min. switching level high signal	[V] 10
Digital inputs protected against short circuits	yes

AC2251

AS-Interface control cabinet module

SmartL25 4DI 4DO T C



Outputs				
Number of digital outputs			4	
Circuit			PNP	
Voltage range DC [V]			20...30; (external (E+/E-), to PELV)	
Max. current load per output [mA]			1000; (utilisation category DC-12: 700 mA; utilisation category DC-13 (control of electromagnets): 20 W (IEC 60947-5-1))	
Short-circuit proof			yes	
Electrically separated			yes	
Operating conditions				
Ambient temperature [°C]			-25...70	
Note on ambient temperature			cRUus: -25...60 °C	
Protection			IP 20	
Tests / approvals				
EMC		EN 50295		
MTTF [years]			184	
AS-i classification				
AS-i version			2.1	
AS-i addressing			addressing socket	
Extended addressing mode possible			no	
AS-i profile			S-7.0.E	
AS-i I/O configuration [hex]			7	
AS-i ID code [hex]			0.E	
AS-i certificate			37301	
Assignment of the data bits		data bit	D0	D1
		input	I-1	I-2
		Output	O-1	O-2
				D2
				D3
				I-4
				O-3
				O-4
Mechanical data				
Weight [g]			141	
Type of mounting			mounting on DIN rail; string mounting possible	
Materials			PA	
Displays / operating elements				
Display		switching status		LED, yellow
		operation		LED, green
		errors		LED, red
Accessories				
Accessories (optional)			COMBICON connectors	
Remarks				
Remarks			Inputs and outputs must be electrically isolated. Do not connect any of the following points to an external potential: I-, I+, I1, I2, I3, I4 The connections are electrically connected with the AS-i cable.	
Pack quantity			1 pcs.	

AC2251



AS-Interface control cabinet module

SmartL25 4DI 4DO T C

Electrical connection

COMBICON:

Connection

I-	I-	I-	I-
I1	I2	I3	I4
I+	I+	I+	I+

O-	O-	O-	O-
O1	O2	O3	O4
A+	A-	E+	E-

A+	AS-i +
A-	AS-i -
I+	Sensor supply +24V
I-	Sensor supply 0V
E+	actuator supply +24V
E-	actuator supply 0V
I1...I4	switching input sensor 1...4
O1...O4	switching output actuator 1...4
O-	switching output actuator 0V