



ADAPTOR M12 MALE/ M12 FEMALE 4 POLES SHIELDED, I TO U

Adapter
M12 - M12
Male straight to female straight
4-pole, shielded
Current /voltage converter

[Link to Product](#)

Illustration



Product may differ from Image

Form

42251

Technical Data

Operating voltage	max. 24 V AC/DC
Operating current per contact	max. 4 A

Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Compression gland	Zinc die casting, matte nickel plated
Protection	IP67 inserted and tightened (EN 60529)
Material	PUR
Shielded	yes
Application	Current /voltage converter

General data

Temperature range	-25...+85 °C
Test isolation voltage	0.8 kVrms

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1