

## MTS 1-PHASE CONTROL AND ISOLATION TRANSFORMER


P: 100VA IN: 208...550VAC OUT: 24VAC

Single-phase - Control and Isolation Transformers  
100 VA  
Isolation class T 40/B


Other voltages on request.

### [Link to Product](#)

#### Illustration



stay connected



Product may differ from Image

### Input

|                       |  |
|-----------------------|--|
| Input voltage         | 208, 230, 380, 400, 420, 440, 460, 480, 500, 525, 550 V AC |
| Input current         | 0.57 A (208 V AC); 0.21 A (550 V AC)                       |
| Inrush current        | 9.7 A (208 V AC); 3.7 A (550 V AC)                         |
| Short-circuit current | 7.6 A (208 V AC); 2.9 A (550 V AC)                         |
| Frequency             | 50...60 Hz   |

### General data

|                          |   |
|--------------------------|---|
| Standards                | (EN 61558-1), (EN 61558-2-6), (EN 62041 category 0) |
| Test isolation voltage   | 6.3 kV (prim./sec.)                                 |
| Mounting method          | Key-hole mounting                                   |
| Dimensions H x W x D     | 88x84x93  |
| Fixing centers a x b x c | 64.5x64x4.8   |
| Drill hole Ø             | 4.8x8.4   |
| Temperature range        | -20...+40 °C (storage temperature -40...+80 °C)     |

### Output

|                |         |
|----------------|---------|
| Output voltage | 24 V AC |
|----------------|---------|

### Commercial data

|                        |          |
|------------------------|----------|
| country of origin      | CZ       |
| customs tariff number  | 85043180 |
| minimum order quantity | 1        |