

SIVACON, base, with cut-outs for flanges, IPXX, D: 600 mm, W: 900 mm, galvanized




Figure similar

| Model | |
|--|---------------------------|
| Product brand name | SIVACON |
| Design of the product | With cut-outs for flanges |
| Design of the surface | galvanized |
| Design of the product / EMC version | No |
| Protection class IP | IPXX |
| Product component | No |
| <ul style="list-style-type: none"> • ventilation | |
| Mechanical Design | |
| Width | 900 mm |
| Depth | 600 mm |
| Net weight | 6 800 g |
| Equipment marking | |
| <ul style="list-style-type: none"> • acc. to DIN EN 61346-2 | U |
| <ul style="list-style-type: none"> • acc. to DIN EN 81346-2 | UC |

| EMC | Declaration of Conformity | Test Certificates | other |
|-------------------------------|---|--|-------------------------------|
| Miscellaneous |  EG-Konf. | Special Test Certificate | Miscellaneous |

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1096-2UB52-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1096-2UB52-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1096-2UB52-0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

