

OUTDOOR

Model	OGL 130 CG
Type	outdoor globe light - colour
Market	EU
EAN code	8718781553654
HS code (Intrastat)	9405403990
Wattage W	4,6W
Wattage Energylabel kWh	5 kWh/1000h
Standby power W	0.20 W
Input Voltage	24V DC
Operating Voltage	24V DC
Number of LEDs (per unit)	7+7 LED's (7 white + 7 RGB)
Frequency	50/60 Hz
Lifespan	> 30.000 hrs
Switching cycles (Schaltzyklen)	n.a.
Replacement wattage (of the light source)	33 W
Lumen (per unit)	370 lm
Lumen (total product)	370 lm
Dimming range	1 ‰ -100 ‰
Powersupply	220-240V AC - 24V DC - 1.0A (24W max.)
Expandable products	max. 5 globe lights
Expandable cable length	max. total cable length is 35m
CCT	RGB + 1800K-6500K white
CRI	CRI > 95
Beam angle	260°
Operating temperature	-20-+40°C
IP rating	IP65
IP rating IZCB	n.a.
IP rating plug	IP44
Dimensions product	∅ 190mm
Dimensions IZCB (excl. Wires)	n.a.
Housing materials product (spot/pedestal/globe)	plastic
Housing materials IZCB	plastic (ABS)
Weight product (incl. wire)	360 gr

Weight IZCB (incl. wires) n.a.
cable length product (spot/pedestal/globe) 50cm
cable length IZCB - cable product n.a.

cable length powersupply - IZCB n.a.
cable length between the spots/pedestal/globe 2m
Smart communication protocol n.a.

Energy Label (new)



QR code - EPREL database



EPREL ID 1017159


Energy Label (old) n.a.


Country of Origin Made in China

CE or UK CA 

WEEE symbol 

Recycle logo 1 

Recycle logo 2 (Grüne Punkt - DE) 

Recycle logo 3 (Triman - FR) 

Protection Class Power Supply n.a.

Protection Class IZCB n.a.